Clean Tubing: Soft Polyolefin Tubing TPS Series





Complies with FDA (Food and Drug Administration) §175.300 dissolution test

_	 Applicable —: Non-conformance
White (W)	•
Black (B)	_
Red (R)	_
Blue (BU)	•
Yellow (Y)	•
Green (G)	_

Model/Specifications

● — 20 m roll □ — 100 m roll

Model	TPS0425	TPS0604	TPS0805	TPS1065	TPS1208			
O.D. (mm)	4	6	8	10	12			
I.D. (mm)	2.5	4	5	6.5	8			
White (W)		•	•	•				
Black (B)		•	•	•				
Red (R)		•	•	•				
Blue (BU)		_	<u> </u>	_				
Yellow (Y)	—	_		_				
Green (G)	—	<u> </u>	_		<u> </u>			
Fluid	Air/Nitrogen gas/Water/DI water (Pure water) (1)							

Fluid		Air/Nitrogen gas/Water/DI water (Pure water) (1)						
Max.	20°C			0.	7			
operating	40°C	0.58						
pressure	60°C	0.46						
(MPa)	80°C		0.33					
Min. bending rad	dius (mm)	10	20	2	5 (30	4	0
Applicable fi	ttings	Clean one-touch fittings One-touch fittings, Metal: KQB2 series One-touch fittings, Stainless steel 316: KQG2 series Insert fittings						
Operating tem	perature	– 20 to 80°C, For water 5 to 80°C						

Note 1) Please consult with SMC regarding other fluids.

Material


Note 2) Abnormal temperature rise caused by adiabatic compression may result in the tube

Polyolefin resin


Note 3) The minimum bending radius indicates the value at a temperature of 20°C with an outside diameter rate of change of 10% or less.

Note 4) Polyolefin resin is not suitable for regular pneumatic equipment piping because it is not resistant to mineral oil.

Max. Operating Pressure



How to Order



Green (Opaque)

KQB2

KQ2

KM

KF M

H/DL L/LL KC

KK

KK130 DM KDM

KB

KR KA

KQG2

KG KFG2

MS

KKA

KΡ

LO

MQR

IDK

G